


# STATOVISION®

High-resolution representation of surfaces brings hidden defects to light



## Highlights

- Intelligent filter algorithms for targeted suppression of interfering contours like drill holes, grooves, bevels, etc.
- High-resolution representation of the component surface
- Digital filters with large dynamic range
- Post-data analysis for process improvement, since raw data can be stored and post-processed
- Report creation in PDF, PNG and CSV formats

## New dimensions in component testing

With STATOVISION, FOERSTER offers an innovative software solution for the identification and visualization of heretofore undetectable errors. Intelligent filter algorithms enable previously impossible inspection tasks; since this allows interference signals to be filtered out and suppressed, cracks near drill holes or millings, for example, can be found. Furthermore, by superimposing the images of several components, it is possible to identify – at an early stage – patterns in the defects, e.g. due to tool wear, so that the source of the error can be eliminated.

# Testing with STATOVISION


## For example on drilled brake discs

### Testing with STATOVISION

Previously, drilled brake discs could only be inspected if large regions were blanked out, meaning that certain areas remained untested. Cracks in or around the drill holes went completely unnoticed during the inspection process. Now, the STATOVISION software can “learn” about such interfering contours as drill holes, grooves or milled features. Then, in the testing step during production, these learned areas are intentionally suppressed. This makes it possible – for the first time – to reliably detect and display cracks or other surface defects that are located near or between the drill holes.

### Clear C-scan representation

A high-resolution C-scan clearly displays the quality of the component's surface. Defects can thus be located precisely. The data is then saved to produce comprehensive statistics and complete documentation to ensure traceability. By superimposing several images on top of each other, disruptive process effects (e.g. tool wear) can also be detected and eliminated early on to lower reject rates.



### Headquarters

- Institut Dr. Foerster GmbH & Co. KG, Germany

### Subsidiaries

- Magnetische Pruefanlagen GmbH, Germany
- FOERSTER France SAS, France
- FOERSTER U.K. Limited, United Kingdom
- FOERSTER Italia S.r.l., Italy
- FOERSTER Russland AO, Russia
- FOERSTER Tecom, s.r.o., Czech Republic
- FOERSTER (Shanghai) NDT Instruments Co., Ltd., China
- FOERSTER Japan Limited, Japan
- NDT Instruments Pte Ltd, Singapore
- FOERSTER Instruments Inc., USA

The FOERSTER Group is represented by subsidiaries and qualified agents in over 60 countries.

### Magnetische Pruefanlagen GmbH

In Laisen 65  
72766 Reutlingen  
Germany  
+49 7121 1099 0  
info@mp-ndt.de  
www.mp-ndt.de

